

ZB 5,LGS:FORTL.ZAHLEN 261-270 - Zack marker strip

1050017:0261

<https://www.phoenixcontact.com/us/products/1050017:0261>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, 10-section, horizontally labeled with the consecutive numbers: 261 ... 270, white, for terminal block width: 5.2 mm, mounting type: latching

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1050017:0261 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG05 |
| Product key | BG2122 |
| GTIN | 4017918506964 |
| Weight per piece (including packing) | 1.35 g |
| Weight per piece (excluding packing) | 1.35 g |
| Customs tariff number | 49119900 |
| Country of origin | DE |

ZB 5,LGS:FORTL.ZAHLEN 261-270 - Zack marker strip



1050017:0261

<https://www.phoenixcontact.com/us/products/1050017:0261>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 5.2 mm |

Marking

| | |
|-----------|-------------|
| Printing | 261 ... 270 |
| Slot type | high |

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

Material specifications

| | |
|--|--------------------------------|
| Color | white (RAL 9010) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life | 2 years |

Dimensions

| | |
|--------|---------|
| Width | 5.15 mm |
| Height | 10.5 mm |
| Depth | 4.20 mm |
| Pitch | 5.2 mm |

Text field

| | |
|-------------------|----------|
| Text field width | 5.15 mm |
| Text field height | 10.50 mm |

Standards and regulations

| | |
|-----------------|--------------|
| Wipe resistance | DIN 30646 |
| | DIN VDE 0611 |

ZB 5,LGS:FORTL.ZAHLEN 261-270 - Zack marker strip



1050017:0261

<https://www.phoenixcontact.com/us/products/1050017:0261>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

ZB 5,LGS:FORTL.ZAHLEN 261-270 - Zack marker strip



1050017:0261

<https://www.phoenixcontact.com/us/products/1050017:0261>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.003 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com