

VS-GC-RJ456A-BUBU - Connector



1055552

<https://www.phoenixcontact.com/us/products/1055552>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Gender changer, RJ45 CAT6A, female/female, shielded



Commercial data

Item number	1055552
Packing unit	1 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Sales key	BF70
Product key	AF7EZ X
GTIN	4055626693149
Weight per piece (including packing)	21.82 g
Weight per piece (excluding packing)	21.82 g
Customs tariff number	85366990
Country of origin	LV

VS-GC-RJ456A-BUBU - Connector



1055552

<https://www.phoenixcontact.com/us/products/1055552>

Technical data

Product properties

Product type	Data front plate
Number of positions	8
Shielded	yes

Electrical properties

Rated voltage (III/3)	max. 30 V AC (RJ45)
Rated current	max. 175 mA (RJ45)
Nominal current I_N	max. 175 mA (RJ45)
Transmission speed	10 Gbps

Dimensions

Width	15.6 mm
Height	34.4 mm
Length	13.2 mm

Material specifications

Material Housing	Die-cast zinc
------------------	---------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750 (RJ45)
-----------------------------	-------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C

VS-GC-RJ456A-BUBU - Connector



1055552

<https://www.phoenixcontact.com/us/products/1055552>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-GC-RJ456A-BUBU - Connector



1055552

<https://www.phoenixcontact.com/us/products/1055552>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com