

P-DI GN - Isolating plug



1071062

<https://www.phoenixcontact.com/us/products/1071062>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Isolating plug, depth: 23.1 mm, width: 3.5 mm, height: 10.8 mm, color: green

Your advantages

- Can be used in all ...-TG disconnect terminal blocks from the CLIPLINE complete system

Commercial data

Item number	1071062
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE2ZWX
GTIN	4055626749891
Weight per piece (including packing)	0.66 g
Weight per piece (excluding packing)	0.62 g
Customs tariff number	85366990
Country of origin	CN

P-DI GN - Isolating plug



1071062

<https://www.phoenixcontact.com/us/products/1071062>

Technical data

Product properties

Product type	Knife
--------------	-------

Dimensions

Width	3.5 mm
Height	10.8 mm
Depth	23.1 mm

Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94	V2
Insulating material	PA
Static insulating material application in cold	-40 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

P-DI GN - Isolating plug

1071062

<https://www.phoenixcontact.com/us/products/1071062>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1071062>

 CSA Approval ID: 158887				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	-	15 A	-	-

P-DI GN - Isolating plug



1071062

<https://www.phoenixcontact.com/us/products/1071062>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

P-DI GN - Isolating plug

1071062

<https://www.phoenixcontact.com/us/products/1071062>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.004 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com