

IPC 24VDC DESKTOP POWER US - Power supply unit



1075579

<https://www.phoenixcontact.com/us/products/1075579>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

24 V DC desktop power supply for use in North America



Your advantages

- Meets Energy Star EPS 2.0/ErP lot 7
- Meets DOE Level VI
- EMC standard: EN 55022 Class B/EN 55024 Class B
- Overcurrent protection
- Over temperature protection
- Surge protection

Commercial data

Item number	1075579
Packing unit	100 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR12
Product key	DRBABZ
GTIN	4055626779072
Weight per piece (including packing)	692 g
Weight per piece (excluding packing)	9,999 g
Customs tariff number	85044083
Country of origin	CN

IPC 24VDC DESKTOP POWER US - Power supply unit



1075579

<https://www.phoenixcontact.com/us/products/1075579>

Technical data

Electrical properties

Rated current	6.25 A
---------------	--------

Supply

Supply voltage range	90 V AC ... 264 V AC
----------------------	----------------------

Product properties

Product type	Power supply
--------------	--------------

Dimensions

Width	72 mm
Height	42 mm
Depth	171 mm

Material specifications

Color	black
-------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 80 °C
Permissible humidity (operation)	20 % (non-condensing)
Permissible humidity (storage/transport)	10 % (non-condensing)

IPC 24VDC DESKTOP POWER US - Power supply unit



1075579

<https://www.phoenixcontact.com/us/products/1075579>

Classifications

ECLASS

ECLASS-13.0	27242209
ECLASS-15.0	27242209

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

IPC 24VDC DESKTOP POWER US - Power supply unit



1075579

<https://www.phoenixcontact.com/us/products/1075579>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com