

FOC-FR19:1U-OS4S-LCD2-OM1 - 19" mounting frame




1076661

<https://www.phoenixcontact.com/us/products/1076661>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fiber optic distribution box, type: 19"-rack mount fiber optic distribution box, degree of protection: IP20, number of positions: 1*4, marking material: aluminum, color: gray



Your advantages

- Fast and reliable cabling, thanks to clear connections on the front
- With threaded locking latch

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1076661 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB15 |
| Product key | ABNHAC |
| GTIN | 4055626784854 |
| Weight per piece (including packing) | 1,756.082 g |
| Weight per piece (excluding packing) | 1,756.082 g |
| Customs tariff number | 85367000 |
| Country of origin | CN |

1076661

<https://www.phoenixcontact.com/us/products/1076661>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Network distributor box |
| Type | 1RU |
| Number of positions | 4 |

Material specifications

| | |
|--|----------------|
| Color | gray |
| Flammability rating according to UL 94 | V0 |
| Housing material | Aluminum alloy |
| Outer sheath, material | LSFH |

Cable/line

| | |
|------------------------|------------------------------|
| Cable type | Multimode fiberglass |
| Cable type | Fan out |
| Outer sheath, material | LSFH |
| Halogen-free | complying with IEC 60754-1/2 |

FO cable

| | |
|-------------|-------------|
| Fiber type | GOF |
| Attenuation | typ. 0.2 dB |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-----------------------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 85 °C (IEC 61300-2-22) |

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

1076661

<https://www.phoenixcontact.com/us/products/1076661>

Classifications

ECLASS

ECLASS-13.0

19170113

ETIM

ETIM 9.0

EC001130

UNSPSC

UNSPSC 21.0

43223300

1076661

<https://www.phoenixcontact.com/us/products/1076661>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com