

# FOC-FR19:1U-OS4S-LCD2-OM1 - 19" mounting frame




1076661

<https://www.phoenixcontact.com/us/products/1076661>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fiber optic distribution box, type: 19"-rack mount fiber optic distribution box, degree of protection: IP20, number of positions: 1\*4, marking material: aluminum, color: gray



## Your advantages

- Fast and reliable cabling, thanks to clear connections on the front
- With threaded locking latch

## Commercial data

Item number	1076661
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHAC
GTIN	4055626784854
Weight per piece (including packing)	1,756.082 g
Weight per piece (excluding packing)	1,756.082 g
Customs tariff number	85367000
Country of origin	CN

1076661

<https://www.phoenixcontact.com/us/products/1076661>

## Technical data

### Product properties

Product type	Network distributor box
Type	1RU
Number of positions	4

### Material specifications

Color	gray
Flammability rating according to UL 94	V0
Housing material	Aluminum alloy
Outer sheath, material	LSFH

### Cable/line

Cable type	Multimode fiberglass
Cable type	Fan out
Outer sheath, material	LSFH
Halogen-free	complying with IEC 60754-1/2

### FO cable

Fiber type	GOF
Attenuation	typ. 0.2 dB

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)

### Mounting

Mounting type	Screw mounting
---------------	----------------

1076661

<https://www.phoenixcontact.com/us/products/1076661>

## Classifications

### ECLASS

ECLASS-13.0

19170113

### ETIM

ETIM 9.0

EC001130

### UNSPSC

UNSPSC 21.0

43223300

1076661

<https://www.phoenixcontact.com/us/products/1076661>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)