

FBST 50-PLC GY - Single plug-in bridge



1081053

<https://www.phoenixcontact.com/us/products/1081053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Single plug-in bridge, nominal current: 32 A, length: 50 mm, color: gray



Commercial data

Item number	1081053
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	C461
Product key	DK62Z1
GTIN	4055626807911
Weight per piece (including packing)	4.41 g
Weight per piece (excluding packing)	1.6 g
Customs tariff number	85366990
Country of origin	DE

FBST 50-PLC GY - Single plug-in bridge



1081053

<https://www.phoenixcontact.com/us/products/1081053>

Technical data

Product properties

Product type	Bridge
--------------	--------

Electrical properties

Maximum load current	32 A
----------------------	------

Connection data

Maximum load current	32 A
----------------------	------

Dimensions

Length	50 mm
--------	-------

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (UL (Haz. Loc.))	-40 °C ... 70 °C
--	------------------

Approvals

UL, USA/Canada

Identification	Class I, Zone 2, AEx ec IIC T4
	Class I, Zone 2, Ex ec IIC Gc T4 X

FBST 50-PLC GY - Single plug-in bridge



1081053

<https://www.phoenixcontact.com/us/products/1081053>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1081053>



cULus Listed

Approval ID: E140324



cULus Listed

Approval ID: E140324



cULus Listed

Approval ID: E199827

FBST 50-PLC GY - Single plug-in bridge



1081053

<https://www.phoenixcontact.com/us/products/1081053>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBST 50-PLC GY - Single plug-in bridge



1081053

<https://www.phoenixcontact.com/us/products/1081053>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com