

HS LCA-RGB-10X5-L - Signal light

1082299

<https://www.phoenixcontact.com/us/products/1082299>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



10 mm signal light with SMD-LED 5 mm (color: RGB) for assembly on wall thicknesses from 1.5 mm. Black housing made of polycarbonate (UL 94-V0) with four 94 mm tin-plated free wire ends, watertight IP68 (EN 60529)

Commercial data

Item number	1082299
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGABC
GTIN	4055626812632
Weight per piece (including packing)	6.6 g
Weight per piece (excluding packing)	1.035 g
Customs tariff number	85318070
Country of origin	TN

HS LCA-RGB-10X5-L - Signal light



1082299

<https://www.phoenixcontact.com/us/products/1082299>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Light
Number of positions	1
Alignment	flexible
Conductor type	Signal light with litz wires
Head form	Raised head
Number of indicators	1 (1 row x 1 column)

Dimensions

Diameter	10 mm (Aperture diameter)
	5 mm (Lens diameter)
Hole diameter	8 mm ^{H7}
Dimensions	94 mm (Cable ends)

Material specifications

Color (Lens)	transparent
Color (Housing)	black (RAL 9005)
Material Lens	Polycarbonate
Material Housing	Polycarbonate

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP68
Ambient temperature (operation)	-20 °C ... 80 °C

Mounting

Mounting type	Press-in
---------------	----------

Packaging specifications

Type of packaging	PE bag
-------------------	--------

HS LCA-RGB-10X5-L - Signal light



1082299

<https://www.phoenixcontact.com/us/products/1082299>

Classifications

ECLASS

ECLASS-13.0	27110350
ECLASS-15.0	27110350

ETIM

ETIM 10.0	EC002975
-----------	----------

UNSPSC

UNSPSC 21.0	32151500
-------------	----------

HS LCA-RGB-10X5-L - Signal light



1082299

<https://www.phoenixcontact.com/us/products/1082299>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com