

RTU READY UPS 161408 - Control cabinet



1094596

<https://www.phoenixcontact.com/us/products/1094596>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Prewired control cabinet with power supply, battery backup, surge protective device, and circuit breaker for use with remote control and monitoring devices



RTU READY... 181610 version shown

Product description

To simplify the selection and installation of wireless devices, Phoenix Contact offers the RTU READY... enclosure system to house radios, PLCs, or other control products. The prewired control cabinet provides a 24 V DC power supply and surge protection for line power and antenna connections, and terminal blocks for easy connectivity, all mounted on standard NS 35 mounting rail.

The selected components provide a robust housing with reliable power. Simply add a radio, antenna, or controller to complete the system.

Your advantages

- 100 V AC ... 240 V AC nominal input voltage range
- UPS with 24 V DC backup battery
- Supply voltage: 24 V DC
- Prewired cabinetry with extra terminal blocks for simple, flexible installation
- UL 508A Listed
- COAXTRAB surge protection for antenna connection

Commercial data

Item number	1094596
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DT02
Product key	DTHDCA
GTIN	4063151030728
Weight per piece (including packing)	0.01 g
Weight per piece (excluding packing)	0.01 g
Country of origin	US

RTU READY UPS 161408 - Control cabinet



1094596

<https://www.phoenixcontact.com/us/products/1094596>

Set consists of

UNO-PS/1AC/24DC/90W/C2LPS - Power supply

2902994

<https://www.phoenixcontact.com/us/products/2902994>



Primary-switched power supply unit UNO POWER, Screw connection, DIN rail mounting, input: 1-phase, output: 24 V DC / 3.75 A

RTU READY UPS 161408 - Control cabinet

1094596

<https://www.phoenixcontact.com/us/products/1094596>



Prewired control cabinet with power supply, battery backup, surge protective device, and circuit breaker for use with remote control and monitoring devices

1094596

<https://www.phoenixcontact.com/us/products/1094596>

Technical data

Notes

Trade restriction

CE note

The products are offered exclusively for export outside the EU and the European Economic Area.

Product properties

Product type

Control box

Electrical properties

Supply

Supply voltage range

85 V AC ... 264 V AC

Typical current consumption

3.75 A

Dimensions

Width

384 mm

Height

443 mm

Depth

221 mm

Material specifications

Housing material

PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

-15 °C ... 50 °C

Standards and regulations

Standards

Standards/regulations

UL 508A

RTU READY UPS 161408 - Control cabinet



1094596

<https://www.phoenixcontact.com/us/products/1094596>

Classifications

ECLASS

ECLASS-13.0	27370190
-------------	----------

RTU READY UPS 161408 - Control cabinet



1094596

<https://www.phoenixcontact.com/us/products/1094596>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com