

UCS PED 9005 VPE10 - Stand

1099257

<https://www.phoenixcontact.com/us/products/1099257>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Stand for mounting the UCS housing; height: 47 mm; material: polyamide; color: black, similar to RAL 9005; panel mounting option is integrated, snaps into the screw holes of the housing



Your advantages

- Practical customization options
- Tool-free snap-in principle enables easy mounting on the device panel
- Flexible mounting options for the control cabinet and use in the field
- Can be adapted to suit the application, thanks to identical receptacles in the housing
- Different colors for high recognition value inside and outside the control cabinet

Commercial data

Item number	1099257
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ACFCAZ
GTIN	4055626945675
Weight per piece (including packing)	28.6 g
Weight per piece (excluding packing)	27 g
Country of origin	DE

UCS PED 9005 VPE10 - Stand

1099257

<https://www.phoenixcontact.com/us/products/1099257>



Technical data

Notes

Assembly note	Please observe the application note in the download area.
General	The UCS PED... stand has drill holes that are also suitable for panel mounting. Recommended screws for panel mounting: S5 dowel, screw $\varnothing$ 4.0 mm.

Product properties

Product type	Mounting material
Housing type	Universal housings
Housing series	UCS
Ventilation openings present	no

Dimensions

Width	90 mm
Height	37.5 mm
Depth	19.2 mm
Diameter mounting hole	4 mm

Material specifications

Color (Housing)	black (RAL 9005)
Material	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Snap in
Mounting position	Panel mounting

Packaging specifications

Type of packaging	PE bag
-------------------	--------

UCS PED 9005 VPE10 - Stand



1099257

<https://www.phoenixcontact.com/us/products/1099257>

Classifications

ECLASS

ECLASS-13.0	27190605
-------------	----------

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UCS PED 9005 VPE10 - Stand

1099257

<https://www.phoenixcontact.com/us/products/1099257>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.283 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com