
PSR-M-CABLE25 - Cable

1104855

https://www.phoenixcontact.com/us/products/1104855

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a version of the article

Connection cable for TBUS extension in connection with PSR-M-TBUS1 or PSR-M-TBUS2, 25 m

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	1104855
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN02
Product key	DNA366
GTIN	4055626973012
Weight per piece (including packing)	2,359 g
Weight per piece (excluding packing)	2,359 g
Customs tariff number	85444995
Country of origin	IT

Technical data

Notes

Note on application

Note on application	Only for industrial use

Product properties

Product type	Adapter cable

Electrical properties

Impedance	nom. 120 Ω

Dimensions

External dimensions

External diameter max.	9.00 mm

Material specifications

Outer sheath, material	PVC

Cable/line

Cable length	25 m
Cable structure	2 x 2 x 24 AWG
External cable diameter	8.70 mm
Outer sheath, material	PVC
External sheath, color	yellow
Shielding	Braided copper wires
Cable resistance	< 95 mΩ/m

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886

UNSPSC

UNSPSC 21.0	39121100

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	9.12 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com