

BL2 BPC 3100 - Box PC



1105776

<https://www.phoenixcontact.com/us/products/1105776>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP20-rated fanless industrial box PC (BPC) with energy-efficient Intel® Core™ i3-6100U processor with 8 GB of RAM and M.2 mass storage.



Commercial data

Item number	1105776
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR20
Product key	DRBABA
Weight per piece (including packing)	500 g
Weight per piece (excluding packing)	450 g
Customs tariff number	84715000
Country of origin	TW

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Box PC
--------------	--------

Computer data

Processor	Intel® Core™ i3-6100U
Operating system	Windows® 10 IoT Enterprise LTSC 2019 (64-bit), Multi-language
RAM	8 GB DDR3
Data storage system	M.2 SSD
Cooling	passive

System properties

User software	without user software
	Visu+

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Power supply unit	24 V DC ±20 %
-------------------	---------------

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Interfaces

Interfaces	1x COM (RS-232/422/485)
	2x COM (RS-232)
	2x USB 2.0
	2x USB 3.0
Monitor output	2x DisplayPort
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

Dimensions

External dimensions

Width / Height / Depth	247 mm / 145 mm / 54 mm
------------------------	-------------------------

Installation dimensions

Width / Height / Installation depth	247 mm / 94 mm /
-------------------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	10 % ... 90 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 90 % (non-condensing)
Shock	20g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	2g _{rms} at sine, 5~500 Hz, 1 h/axis (panel mounting; SSD operating) according to EN 60068-2-6 0.5g _{rms} at sine, 5~500 Hz, 1 h/axis (panel mounting; HDD operating) according to EN 60068-2-6

Mounting

Mounting type	Panel mounting
---------------	----------------

BL2 BPC 3100 - Box PC




1105776

<https://www.phoenixcontact.com/us/products/1105776>

Drawings

Dimensional drawing



BL2 BPC 3100 - Box PC



1105776

<https://www.phoenixcontact.com/us/products/1105776>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1105776>



IECEE CB Scheme

Approval ID: US-37343-M1-UL



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705

BL2 BPC 3100 - Box PC



1105776

<https://www.phoenixcontact.com/us/products/1105776>

Classifications

ECLASS

ECLASS-13.0

19200102

ETIM

ETIM 9.0

EC001413

UNSPSC

UNSPSC 21.0

43211500

1105776

<https://www.phoenixcontact.com/us/products/1105776>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	1-Methyl-2-pyrrolidone (NMP)(CAS: 872-50-4)
	Lead(CAS: 7439-92-1)
	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one(CAS: 71868-10-5)

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com