

SAC-5P-15,0-115/M 8FRB - Sensor/actuator cable



1107220

<https://www.phoenixcontact.com/us/products/1107220>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1107220 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF01 |
| Product key | AF1BDA |
| GTIN | 4063151007416 |
| Weight per piece (including packing) | 457.4 g |
| Weight per piece (excluding packing) | 457.4 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

SAC-5P-15,0-115/M 8FRB - Sensor/actuator cable



1107220

<https://www.phoenixcontact.com/us/products/1107220>

Technical data

Product properties

| | |
|--------------|-----------------------|
| Product type | Sensor/actuator cable |
|--------------|-----------------------|

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 30 V AC |
| | 30 V DC |
| Nominal current I_N | 3 A |

Connection data

Conductor connection

| | |
|-------------------|--------|
| Tightening torque | 0.2 Nm |
|-------------------|--------|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP65 |
| | IP67 |
| | IP68 |

SAC-5P-15,0-115/M 8FRB - Sensor/actuator cable



1107220

<https://www.phoenixcontact.com/us/products/1107220>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-5P-15,0-115/M 8FRB - Sensor/actuator cable



1107220

<https://www.phoenixcontact.com/us/products/1107220>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com