

SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/us/products/1108101>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection with M12 standard thread, push-pull, with O-ring, for 2-piece K-, L-, and M-coded THR contact carriers

Your advantages

- Plug and Produce: quick and reliable connection even in confined spaces
- Easy design-in: countersunk M12 ports for compact device concepts
- Highly future-proof: standardized product range for worldwide availability
- Greater flexibility: one M12 device connection for screw and push-pull connectors
- Time savings of 80% during installation compared to screw connection

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1108101 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | AB23 |
| Product key | ABQABC |
| GTIN | 4063151011499 |
| Weight per piece (including packing) | 10.99 g |
| Weight per piece (excluding packing) | 9.798 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/us/products/1108101>

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
| Order information: | Lock nut is included in the scope of delivery |

Product properties

| | |
|--------------|----------------------------|
| Product type | Circular connector housing |
| Thread type | M12 |

Connection data

| | |
|-------------------|------------------------|
| Connection method | THR and wave soldering |
| Tightening torque | 1.5 ... 2 Nm |

Material specifications

| | |
|--|----------------------|
| Material | Brass, nickel-plated |
| Flammability rating according to UL 94 | V0 |
| Seal material | FKM |
| Material of grip body | Brass, nickel-plated |
| Material for screw connection | Brass, nickel-plated |

Connector

Connection 1

| | |
|-------------------|----------------------------|
| Head design | Pin |
| Head thread type | M12 |
| Head locking type | Push-pull external locking |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection (when plugged in) | IP67 (correctly plugged in and locked) |
| Degree of protection | IP67 (correctly plugged in and locked) IP67, when in locked state |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation) |
| UL Type Rating | Type 4 (indoor use only) |

SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/us/products/1108101>

Standards and regulations

| | |
|--------------------------|--|
| Standard designation | M12 circular connector |
| Standards/specifications | based on IEC 61076-2-010 Ed. 2 - draft |
| Note | Push-pull |

Mounting

| | |
|---------------|-------------------------|
| Mounting type | Rear mounting (M15 x 1) |
|---------------|-------------------------|

SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/us/products/1108101>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440224 |
| ECLASS-15.0 | 27440224 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003556 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/us/products/1108101>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com