

SAC-3P-M12MR/5-PUR/BI-1L-Z 180 - Sensor/actuator cable



1148446

<https://www.phoenixcontact.com/us/products/1148446>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, Plug angled M12, on Valve connector BI (11 mm), with 1 LED, Wiring: Z diode, cable length: 5 m, Pin connector pattern of valve plug rotated 180°

Commercial data

Item number	1148446
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1DDA
GTIN	4063151139742
Weight per piece (including packing)	181.75 g
Weight per piece (excluding packing)	181.75 g
Country of origin	PL

SAC-3P-M12MR/5-PUR/BI-1L-Z 180 - Sensor/actuator cable



1148446

<https://www.phoenixcontact.com/us/products/1148446>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	3

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Outer sheath, material	PUR
------------------------	-----

Electrical properties

Nominal voltage U_N	24 V AC
	24 V DC
Nominal current I_N	4 A

Connector

Connection 1

Type	Plug angled M12
Number of positions	3

Connection 2

Type	Valve connector BI (11 mm)
Number of positions	3
Protective circuit	Z diode

Cable/line

Cable length	5 m
Outer sheath, material	PUR
External sheath, color	black RAL 9005

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

SAC-3P-M12MR/5-PUR/BI-1L-Z 180 - Sensor/actuator cable



1148446

<https://www.phoenixcontact.com/us/products/1148446>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-3P-M12MR/5-PUR/BI-1L-Z 180 - Sensor/actuator cable



1148446

<https://www.phoenixcontact.com/us/products/1148446>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)
SCIP	32756441-d5d5-434f-8864-c8aaafb8dbb5

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com