

SACC-FP-M-M12/PRESS THR PW PP - Housing screw connection



1189612

<https://www.phoenixcontact.com/us/products/1189612>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Housing screw connection, Pin, M12-Push-pull external locking, THR solder connection



Your advantages

- Plug and Produce: quick and reliable connection even in confined spaces
- Easy design-in: countersunk M12 ports for compact device concepts
- Highly future-proof: standardized product range for worldwide availability
- Greater flexibility: one M12 device connection for screw and push-pull connectors
- Time savings of 80% during installation compared to screw connection

Commercial data

Item number	1189612
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB23
Product key	ABQAAG
GTIN	4063151236861
Weight per piece (including packing)	9.155 g
Weight per piece (excluding packing)	9.155 g
Customs tariff number	85366990
Country of origin	DE

SACC-FP-M-M12/PRESS THR PW PP - Housing screw connection



1189612

<https://www.phoenixcontact.com/us/products/1189612>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Circular connector housing
Thread type	M12

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Material specifications

Flammability rating according to UL 94	V0
Material of grip body	Brass, nickel-plated
Material for screw connection	Brass, nickel-plated

Connector

Connection 1

Head design	Pin
Head thread type	M12
Head locking type	Push-pull external locking

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67, when in locked state
	IP65, when in locked state

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	based on IEC 61076-2-010 Ed. 2 - draft

Mounting

Mounting type	Front mounting
---------------	----------------

SACC-FP-M-M12/PRESS THR PW PP - Housing screw connection



1189612

<https://www.phoenixcontact.com/us/products/1189612>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 10.0	EC003556
-----------	----------

UNSPSC

UNSPSC 21.0	31171600
-------------	----------

SACC-FP-M-M12/PRESS THR PW PP - Housing screw connection



1189612

<https://www.phoenixcontact.com/us/products/1189612>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com