# SF-SOCKET SET 47 - Tool set

1200292

https://www.phoenixcontact.com/us/products/1200292

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



1/4" socket set, 47-piece, 1/4" reversible ratchet, 48 teeth with fast locking system, 50 mm and 100 mm 1/4" extensions, 1/4" screwdriver handle, 150 mm 1/4" flexible extension, 1/4" Cardan joint, 1/4" T-handle
2 x 1/4" bit adapter, 13 knurled 1/4" sockets, wrench size: 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, 21 knurled socket bits: 6 x Torx® T10, T15, T20, T25, T30, T40, 6 x Hex 3, 4, 5, 6, 7, 8 mm, 3 x Phillips recess® PH1, PH2, PH3, 3 x Pozidriv® PZ1, PZ2, PZ3, 3 x slotted 4, 5.5, 7 mm, Allen wrench Hex 1.27, 1.5, 2, 2.5 mm, breakage and impact-resistant plastic case with metal fastening

## Your advantages

- Robust cases for safe storage
- Ratcheting mechanism with 48 teeth enables precise working, even in tight working environments
- Made from chrome vanadium steel for a long service life
- Solid 1/4" screw set with comprehensive equipment
- Optimum power transmission without damaging the screw head, thanks to special edge geometries

## Commercial data

| | |
|---|---|
| Item number | 1200292 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH314G |
| GTIN | 4055626388113 |
| Weight per piece (including packing) | 1,609 g |
| Weight per piece (excluding packing) | 1,603.4 g |
| Customs tariff number | 82060000 |
| Country of origin | TW |

## Technical data

### Notes

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

| | |
|---|---|
| Product type | Tool set |
| Type of packaging | Case |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1200292

**EAC**
Approval ID: RU C-DE.AI30.B.01750

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21045003 |
| ECLASS-15.0 | 21045003 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000149 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27113200 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 20.142 kg CO2e |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com