# VAH - Cover profile carrier

1201468

https://www.phoenixcontact.com/us/products/1201468

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Adjustable cover holder, for mounting covers (up to 3 mm thick) on terminal blocks, can be used for CLIPFIX 35 and E/UK

## Your advantages

- Large-surface labeling with AP-ES insert strips
- Cover profiles provide protection against unauthorized actuation of terminal strips

## Commercial data

| | |
|---|---|
| Item number | 1201468 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE07 |
| Product key | BE61ZX |
| GTIN | 4017918017347 |
| Weight per piece (including packing) | 8.13 g |
| Weight per piece (excluding packing) | 7.4 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

# Technical data

## Product properties

| | |
|---|---|
| Product type | Cover profile |

## Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Static insulating material application in cold | -40 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 125 °C |


## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

## Drawings

Dimensional drawing



## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27371392 |
| ECLASS-15.0 | 27371392 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002886 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121100 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.031 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com