CRIMPFOX ZA 2 - Crimping pliers

1201853

https://www.phoenixcontact.com/us/products/1201853

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09

Commercial data

Item number	1201853
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4017918017552
Weight per piece (including packing)	270.5 g
Weight per piece (excluding packing)	261.2 g
Customs tariff number	82032000
Country of origin	DE

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Square crimp
Min. cross section	0.5 mm²
Max. cross section	6 mm²

Connection data

Conductor connection

Cross section range, metric	0.5 mm² ... 6 mm²

Dimensions

Length	195 mm

Material specifications

Color	black/green
Material	Steel with plastic handle

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1201853

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	4.514 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com