

CRIMPSET 25 - Tool set



1202580

<https://www.phoenixcontact.com/us/products/1202580>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assortment box, metal, supplied with ferrules acc. to DIN 46228-4, 300 pcs. AI 10-12 RD, 200 pcs. AI 16-12 BU, 100 pcs. AI 25-16 YE, as well as WIREFOX-D 40 stripping blade, CRIMPFOX 25R crimping pliers

Product description

Tool set, equipped

Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools

Commercial data

Item number	1202580
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4017918017934
Weight per piece (including packing)	3,075 g
Weight per piece (excluding packing)	2,948 g
Customs tariff number	82060000
Country of origin	SE

CRIMPSET 25 - Tool set

1202580

<https://www.phoenixcontact.com/us/products/1202580>

Set consists of

AI 10 -12 RD - Ferrule

3200551

<https://www.phoenixcontact.com/us/products/3200551>



Ferrule, Length contact range: 12 mm, sleeve length: 22 mm, color: red

AI 16 -12 BU - Ferrule

3200564

<https://www.phoenixcontact.com/us/products/3200564>



Ferrule, Length contact range: 12 mm, sleeve length: 24 mm, color: blue

CRIMPSET 25 - Tool set

1202580

<https://www.phoenixcontact.com/us/products/1202580>



AI 25 -16 YE - Ferrule

3200577

<https://www.phoenixcontact.com/us/products/3200577>

Ferrule, Length contact range: 16 mm, sleeve length: 30 mm, color: yellow



WIREFOX-D 40 - Stripping tool

1212161

<https://www.phoenixcontact.com/us/products/1212161>



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

CRIMPSET 25 - Tool set

1202580

<https://www.phoenixcontact.com/us/products/1202580>



CRIMPFOX 25R - Crimping pliers

1212039

<https://www.phoenixcontact.com/us/products/1212039>



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 10 mm² ... 25 mm², lateral entry, WM crimp

CRIMPSET 25 - Tool set



1202580

<https://www.phoenixcontact.com/us/products/1202580>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Tool set

Compression

WM crimp

Dimensions

Width

357 mm

Height

48 mm

Length

206 mm

Material specifications

Color

silver/matt

Base element material

Metal

CRIMPSET 25 - Tool set



1202580

<https://www.phoenixcontact.com/us/products/1202580>

Classifications

ECLASS

ECLASS-15.0	27400218
ECLASS-13.0	27400218

ETIM

ETIM 10.0	EC000524
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CRIMPSET 25 - Tool set



1202580

<https://www.phoenixcontact.com/us/products/1202580>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com