CRIMPFOX MT 2,5 - Crimping pliers

1204038

https://www.phoenixcontact.com/us/products/1204038

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for crimping conductors to the module female contacts STG-MTN, crimp range: 0.5-2.5 mm^2, AWG: 20-14

Your advantages

- Crimping pliers, for crimping conductors to STG-MTN module socket contacts
- 4 different die stations
- Optimized mechanical transmission reduces the force required by up to 25 %

Commercial data

Item number	1204038
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3137
GTIN	4017918018764
Weight per piece (including packing)	755 g
Weight per piece (excluding packing)	755 g
Customs tariff number	82032000
Country of origin	DE

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	B crimp

Connection data

Conductor connection

Cross section range, metric	0.5 mm² ... 2.5 mm²

Dimensions

Length	270 mm

Material specifications

Color	black

Classifications

ECLASS

ECLASS-13.0	21043811

ETIM

ETIM 9.0	EC000168

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com