CRIMPFOX RC 0,56 - Crimping pliers

1205529

https://www.phoenixcontact.com/us/products/1205529

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for connector contacts 0.08 mm^2 - 0.56 mm^2

Commercial data

Item number	1205529
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3135
GTIN	4017918129132
Weight per piece (including packing)	309.5 g
Weight per piece (excluding packing)	292 g
Customs tariff number	82032000
Country of origin	DE

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Square crimp

Crimping position 1

Min. cross section	0.08 mm²
Max. cross section	0.2 mm²
AWG min	28
AWG max	24

Crimping position 2

Min. cross section	0.2 mm²
Max. cross section	0.56 mm²
AWG min	24
AWG max	20

Connection data

Conductor connection

Cross section range, metric	0.08 mm² ... 0.56 mm²

Dimensions

Width	55 mm
Length	195 mm

Material specifications

Color	black

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1205529

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com