

CUTFOX FB - Cutting tool

1205985

<https://www.phoenixcontact.com/us/products/1205985>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

One-hand bridge cutter, for fixed bridges FBI 10-6, FBI 10-8, FBI 10-10, FBI 10-12



Your advantages

- Precision cutting edge for the corresponding application
- Ergonomically shaped two-component handles for fatigue-free and non-slip use

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1205985 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH311S |
| GTIN | 4017918137755 |
| Weight per piece (including packing) | 196.4 g |
| Weight per piece (excluding packing) | 194.9 g |
| Customs tariff number | 82032000 |
| Country of origin | DE |

CUTFOX FB - Cutting tool

1205985

<https://www.phoenixcontact.com/us/products/1205985>



Technical data

Notes

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Product properties

| | |
|------------------|--|
| Product type | Cutting tool |
| Application | Fixed bridges |
| Product property | Narrow cutting edge |
| | Ergonomic two-component handle |
| | Minimum force required |
| | Special tool steel, die-forged and oil-hardened\ |

Dimensions

| | |
|--------|--------|
| Width | 53 mm |
| Length | 165 mm |

Material specifications

| | |
|-------|----------------------|
| Color | multicolored (RAL -) |
|-------|----------------------|

Cable/line

| | |
|-------------------------|--------|
| External cable diameter | > 0 mm |
|-------------------------|--------|

CUTFOX FB - Cutting tool

1205985

<https://www.phoenixcontact.com/us/products/1205985>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043711 |
| ECLASS-15.0 | 21043711 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000165 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CUTFOX FB - Cutting tool



1205985

<https://www.phoenixcontact.com/us/products/1205985>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 3.005 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com