

CUTFOX 10 120V - Cable-cutting tool



1206832

<https://www.phoenixcontact.com/us/products/1206832>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cutting machine, for cables, litz wires and shrink sleeves, for 120 V mains voltage



The figure shows version CUTFOX 10

Commercial data

Item number	1206832
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	BH3211
GTIN	4017918178864
Weight per piece (including packing)	11.586 kg
Weight per piece (excluding packing)	11.586 kg
Customs tariff number	84798997
Country of origin	DE

CUTFOX 10 120V - Cable-cutting tool



1206832

<https://www.phoenixcontact.com/us/products/1206832>

Technical data

Product properties

Dialog language	German / English / French / Italian
Maximum number of cuts	999
Maximum throughput	8
Section length	2 ... 99999
Host system interface	RS-232
Feed rate	0.5 m/s

Electrical properties

Power consumption	80 VA
-------------------	-------

Supply

Supply voltage	120 V AC
----------------	----------

Connection data

Conductor cross-section flexible	10 mm ² ... 0.08 mm ²
Conductor cross-section rigid	0.08 mm ² ... 2.5 mm ²

Dimensions

Width	194 mm
Height	228 mm
Length	301 mm

Cable/line

External cable diameter	≤ 8.00 mm
-------------------------	-----------

CUTFOX 10 120V - Cable-cutting tool



1206832

<https://www.phoenixcontact.com/us/products/1206832>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com