

# NBC-R4AQ/50,0-94D/OE - Network cable



1211705

<https://www.phoenixcontact.com/us/products/1211705>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, cable length: 50 m, number of positions: 8



## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1211705                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AB11                           |
| Product key                          | ABNABE                         |
| GTIN                                 | 4063151284633                  |
| Weight per piece (including packing) | 2,550.342 g                    |
| Weight per piece (excluding packing) | 2,550.342 g                    |
| Customs tariff number                | 85444290                       |
| Country of origin                    | PL                             |

1211705

<https://www.phoenixcontact.com/us/products/1211705>

## Technical data

### Notes

#### Trade restriction

CE note

The products are offered exclusively for export outside the EU and the European Economic Area.

### Product properties

Product type

Data cable preassembled

Product family

RJ45 INDUSTRIAL IE8 CAT5

Number of positions

8

### Connector

#### Connection 1

Type

Plug straight RJ45

#### Connection 2

Type

free cable end

### Cable/line

Cable length

50.00 m

# NBC-R4AQ/50,0-94D/OE - Network cable



1211705

<https://www.phoenixcontact.com/us/products/1211705>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1211705

<https://www.phoenixcontact.com/us/products/1211705>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |                |
|---------|----------------|
| CO2e kg | 24.701 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)