

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/us/products/1212039>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 10 mm² ... 25 mm², lateral entry, WM crimp

Your advantages

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25 %

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212039 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3131 |
| GTIN | 4046356453905 |
| Weight per piece (including packing) | 681.4 g |
| Weight per piece (excluding packing) | 681.4 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/us/products/1212039>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

| | |
|------------------|---------------------------------|
| Product type | Crimping tool |
| Compression | WM crimp |
| Product property | Low grip span |
| | Up to 25% lower actuation force |

Crimping position 1

| | |
|--------------------|--------------------|
| Max. cross section | 10 mm ² |
| AWG min | 8 |
| AWG max | 4 |

Crimping position 2

| | |
|--------------------|--------------------|
| Max. cross section | 16 mm ² |
| AWG max | 6 |

Crimping position 3

| | |
|--------------------|--------------------|
| Max. cross section | 25 mm ² |
| AWG max | 4 |

Connection data

Conductor connection

| | |
|-----------------------------|---|
| Cross section range, metric | 10 mm ² ... 25 mm ² |
| Cross section range AWG | 8 ... 4 |

Dimensions

| | |
|--------|--------|
| Width | 25 mm |
| Height | 68 mm |
| Length | 256 mm |

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/us/products/1212039>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212039>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/us/products/1212039>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX 25R - Crimping pliers



1212039

<https://www.phoenixcontact.com/us/products/1212039>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com