CRIMPFOX 6S-F - Crimping pliers

1212043

https://www.phoenixcontact.com/us/products/1212043

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.5 mm^2 ... 6 mm^2, front entry, square crimp

Your advantages

- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross-sections
- Unlockable pressure lock
- Comprehensive range of crimping pliers
- Consistently high crimping quality
- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1212043
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4046356453875
Weight per piece (including packing)	460.69 g
Weight per piece (excluding packing)	426.16 g
Customs tariff number	82032000
Country of origin	SE

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Square crimp

Crimping position 1

Min. cross section	0.5 mm²
Max. cross section	6 mm²
AWG min	20
AWG max	10

Connection data

Conductor connection

Cross section range, metric	0.5 mm² ... 6 mm²
Cross section range AWG	20 ... 10

Dimensions


Width	18 mm
Height	59 mm
Length	198 mm

Material specifications

Color	black

Drawings

Product drawing



Classifications

ECLASS

ECLASS-13.0	21043811

ETIM

ETIM 9.0	EC000168

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com