

# CRIMPFOX-M 10/DIE - Crimp insert

1212080

<https://www.phoenixcontact.com/us/products/1212080>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Die, for Crimpfox-M, for ferrules 0.25 - 10 mm<sup>2</sup>, packed in a serial storage box



## Commercial data

Item number	1212080
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Z
GTIN	4046356454506
Weight per piece (including packing)	93.04 g
Weight per piece (excluding packing)	88 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-M 10/DIE - Crimp insert



1212080

<https://www.phoenixcontact.com/us/products/1212080>

## Technical data

### Product properties

Product type	Die
Compression	Trapezoidal crimp
Product property	Replacement insert for CRIMPFOX-M universal crimping pliers

### Crimping position 1

Min. cross section	0.25 mm <sup>2</sup>
Max. cross section	0.75 mm <sup>2</sup>
AWG min	24
AWG max	20

### Crimping position 2

Min. cross section	1 mm <sup>2</sup>
Max. cross section	1.5 mm <sup>2</sup>
AWG min	18
AWG max	16

### Crimping position 3

Max. cross section	2.5 mm <sup>2</sup>
AWG max	14

### Crimping position 4

Max. cross section	4 mm <sup>2</sup>
AWG max	12

### Crimping position 5

Max. cross section	6 mm <sup>2</sup>
AWG max	10

### Crimping position 6

Max. cross section	10 mm <sup>2</sup>
AWG max	8

### Connection data

#### Conductor connection

Cross section range, metric	0.25 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Cross section range AWG	24 ... 8

### Dimensions

Width	75 mm
Height	25.5 mm
Length	114 mm

### Material specifications

# CRIMPFOX-M 10/DIE - Crimp insert

1212080

<https://www.phoenixcontact.com/us/products/1212080>



Color

black

# CRIMPFOX-M 10/DIE - Crimp insert



1212080

<https://www.phoenixcontact.com/us/products/1212080>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212080>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-M 10/DIE - Crimp insert



1212080

<https://www.phoenixcontact.com/us/products/1212080>

## Classifications

### ECLASS

ECLASS-13.0	21043892
ECLASS-15.0	21043892

### ETIM

ETIM 10.0	EC011822
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-M 10/DIE - Crimp insert



1212080

<https://www.phoenixcontact.com/us/products/1212080>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)