

CRIMPFOX-M 10/DIE - Crimp insert

1212080

<https://www.phoenixcontact.com/us/products/1212080>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Die, for Crimpfox-M, for ferrules 0.25 - 10 mm², packed in a serial storage box



Commercial data

Item number	1212080
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Z
GTIN	4046356454506
Weight per piece (including packing)	93.04 g
Weight per piece (excluding packing)	88 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-M 10/DIE - Crimp insert



1212080

<https://www.phoenixcontact.com/us/products/1212080>

Technical data

Product properties

Product type	Die
Compression	Trapezoidal crimp
Product property	Replacement insert for CRIMPFOX-M universal crimping pliers

Crimping position 1

Min. cross section	0.25 mm ²
Max. cross section	0.75 mm ²
AWG min	24
AWG max	20

Crimping position 2

Min. cross section	1 mm ²
Max. cross section	1.5 mm ²
AWG min	18
AWG max	16

Crimping position 3

Max. cross section	2.5 mm ²
AWG max	14

Crimping position 4

Max. cross section	4 mm ²
AWG max	12

Crimping position 5

Max. cross section	6 mm ²
AWG max	10

Crimping position 6

Max. cross section	10 mm ²
AWG max	8

Connection data

Conductor connection

Cross section range, metric	0.25 mm ² ... 10 mm ²
Cross section range AWG	24 ... 8

Dimensions

Width	75 mm
Height	25.5 mm
Length	114 mm

Material specifications

CRIMPFOX-M 10/DIE - Crimp insert

1212080

<https://www.phoenixcontact.com/us/products/1212080>



Color

black

CRIMPFOX-M 10/DIE - Crimp insert



1212080

<https://www.phoenixcontact.com/us/products/1212080>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212080>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-M 10/DIE - Crimp insert



1212080

<https://www.phoenixcontact.com/us/products/1212080>

Classifications

ECLASS

ECLASS-13.0	21043892
ECLASS-15.0	21043892

ETIM

ETIM 10.0	EC011822
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-M 10/DIE - Crimp insert



1212080

<https://www.phoenixcontact.com/us/products/1212080>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com