

# CRIMPFOX-M CX-2/DIE - Crimp insert



1212088

<https://www.phoenixcontact.com/us/products/1212088>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die, for Crimpfox-M, for coaxial connectors (BNC/TNC) RG 58/ 59/ 62/ 71, packed in a serial storage box

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212088       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH313Z        |
| GTIN                                 | 4046356454483 |
| Weight per piece (including packing) | 79.9 g        |
| Weight per piece (excluding packing) | 79.9 g        |
| Customs tariff number                | 82032000      |
| Country of origin                    | SE            |

# CRIMPFOX-M CX-2/DIE - Crimp insert



1212088

<https://www.phoenixcontact.com/us/products/1212088>

## Technical data

### Product properties

|                  |   |
|------------------|---|
| Product type     | Die   |
| Compression      | HEX crimp   |
| Product property | Replacement insert for CRIMPFOX-M universal crimping pliers |
| Crimping width   | 1.69 mm   |
| Crimping width   | 5.41 mm   |
| Crimping width   | 6.48 mm   |

### Connection data

#### Conductor connection

|                             |                     |
|-----------------------------|---------------------|
| Cross section range, metric | > 0 mm <sup>2</sup> |
|-----------------------------|---------------------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 75 mm   |
| Height | 25.5 mm |
| Length | 114 mm  |

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

# CRIMPFOX-M CX-2/DIE - Crimp insert



1212088

<https://www.phoenixcontact.com/us/products/1212088>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212088>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-M CX-2/DIE - Crimp insert



1212088

<https://www.phoenixcontact.com/us/products/1212088>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043892 |
| ECLASS-15.0 | 21043892 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC011822 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX-M CX-2/DIE - Crimp insert



1212088

<https://www.phoenixcontact.com/us/products/1212088>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)