CRIMPFOX-M CX-3/DIE - Crimp insert

1212089

https://www.phoenixcontact.com/us/products/1212089

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die, for Crimpfox-M, for coaxial connectors: CATV RG 6,59, packed in a serial storage box

Commercial data

Item number	1212089
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Z
GTIN	4046356454582
Weight per piece (including packing)	84.8 g
Weight per piece (excluding packing)	81.8 g
Customs tariff number	82032000
Country of origin	SE

Technical data

Product properties

Product type	Die
Compression	HEX crimp
Product property	Replacement insert for CRIMPFOX-M universal crimping pliers
Crimping width	8.23 mm
Crimping width	9.14 mm

Connection data

Conductor connection

Cross section range, metric	> 0 mm²

Dimensions

Width	75 mm
Height	25.5 mm
Length	114 mm

Material specifications

Color	black

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212089

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21043892
ECLASS-15.0	21043892

ETIM

ETIM 10.0	EC011822

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com