# WIREFOX ASI - Stripping tool

1212154

https://www.phoenixcontact.com/us/products/1212154

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping pliers, for AS interface flat-ribbon cables, any desired stripping length

## Your advantages

- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

## Commercial data

| | |
|---|---|
| Item number | 1212154 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3121 |
| GTIN | 4046356454292 |
| Weight per piece (including packing) | 148.8 g |
| Weight per piece (excluding packing) | 148.8 g |
| Customs tariff number | 82032000 |
| Country of origin | DE |

## Technical data

### Notes

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

| | |
|---|---|
| Product type | Stripping tool |
| Application | Standard |
| | PUR |
| | TPE |
| Product property | Automatic adjustment mechanism |
| | Replaceable stripping blade |
| | Any stripping length |

### Connection data

Conductor connection

| | |
|---|---|
| Cross section range, metric | > 0.5 mm² ... 1.5 mm² (Stripping range) |
| | > 0 mm² (Cutting zone) |
| Cross section range AWG | 20 ... 16 (Stripping range) |
| | 16 (Cutting zone) |
| Stripping length | 100 mm |

### Dimensions

| | |
|---|---|
| Width | 25 mm |
| Height | 102 mm |
| Length | 166 mm |

External dimensions

| | |
|---|---|
| Outside diameter | 0 mm ... 1.9 mm |

### Material specifications

| | |
|---|---|
| Color | black |

### Cable/line

| | |
|---|---|
| External cable diameter | > 0 mm ... 1.9 mm |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212154

**EAC**
Approval ID: RU x-DE.xx08.B.02974

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21043706 |
| ECLASS-15.0 | 21043706 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002109 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27111500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 12.97 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com