

TESTFOX CC-1 - Multimeter



1212211

<https://www.phoenixcontact.com/us/products/1212211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Current probe multimeter, for DC and AC voltage measurements, DC and AC current measurements, and resistance measurements, TRUE RMS method of measurement.

Your advantages

- The current probes can be used for voltages of up to 600 V, category III
- All measuring ranges are protected against overload
- They combine the functions of a digital multimeter with those of a current probe
- Enclosed in compact and practical housing, so ideal for use in cramped conditions

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212211 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3332 |
| GTIN | 4046356449809 |
| Weight per piece (including packing) | 501.3 g |
| Weight per piece (excluding packing) | 501.3 g |
| Customs tariff number | 90303100 |
| Country of origin | TW |

Technical data

Notes

| | |
|--------------------|---------------------------------|
| Notes on operation | TRUE RMS methods of measurement |
|--------------------|---------------------------------|

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Product properties

| | |
|---------------|-----------------|
| Product type | Measuring tools |
| Display scope | 4000 digits |

Electrical properties

| | |
|--------------------|------------------------------------|
| Measuring category | CAT III 300 V / CAT II 600 V |
| Power supply | 2 x micro battery 1.5 V, LR03, AAA |

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP30 |
|----------------------|------|

Standards and regulations

| | |
|-------|------------------------------|
| Tests | IEC/EN 61010-1, DIN VDE 0411 |
|-------|------------------------------|

TESTFOX CC-1 - Multimeter



1212211

<https://www.phoenixcontact.com/us/products/1212211>

Classifications

ECLASS

ECLASS-13.0

27200312

ETIM

ETIM 9.0

EC000380

UNSPSC

UNSPSC 21.0

41113600

TESTFOX CC-1 - Multimeter



1212211

<https://www.phoenixcontact.com/us/products/1212211>

Environmental product compliance

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com