

# TESTFOX CC-1 - Multimeter



1212211

<https://www.phoenixcontact.com/us/products/1212211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Current probe multimeter, for DC and AC voltage measurements, DC and AC current measurements, and resistance measurements, TRUE RMS method of measurement.

## Your advantages

- The current probes can be used for voltages of up to 600 V, category III
- All measuring ranges are protected against overload
- They combine the functions of a digital multimeter with those of a current probe
- Enclosed in compact and practical housing, so ideal for use in cramped conditions

## Commercial data

Item number	1212211
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3332
GTIN	4046356449809
Weight per piece (including packing)	501.3 g
Weight per piece (excluding packing)	501.3 g
Customs tariff number	90303100
Country of origin	TW

# TESTFOX CC-1 - Multimeter



1212211

<https://www.phoenixcontact.com/us/products/1212211>

## Technical data

### Notes

Notes on operation	TRUE RMS methods of measurement
Environmental Product Compliance	
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type	Measuring tools
Display scope	4000 digits

### Electrical properties

Measuring category	CAT III 300 V / CAT II 600 V
Power supply	2 x micro battery 1.5 V, LR03, AAA

### Material specifications

Color	black
-------	-------

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP30

### Standards and regulations

Tests	IEC/EN 61010-1, DIN VDE 0411
-------	------------------------------

# TESTFOX CC-1 - Multimeter



1212211

<https://www.phoenixcontact.com/us/products/1212211>

## Classifications

### ECLASS

ECLASS-13.0

27200312

### ETIM

ETIM 9.0

EC000380

### UNSPSC

UNSPSC 21.0

41113600

# TESTFOX CC-1 - Multimeter



1212211

<https://www.phoenixcontact.com/us/products/1212211>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)