

CF 500/DIE TC 4 - Crimp insert

1212237

<https://www.phoenixcontact.com/us/products/1212237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die for CF 500 automatic crimping device, for turned contacts with 2.5 mm and 4.0 mm pin diameter (CK 2,5 ... CK 4,0) 0.14 mm² ... 4 mm²

Commercial data

Item number	1212237
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356449816
Weight per piece (including packing)	67.7 g
Weight per piece (excluding packing)	67.7 g
Customs tariff number	84799070
Country of origin	DE

CF 500/DIE TC 4 - Crimp insert



1212237

<https://www.phoenixcontact.com/us/products/1212237>

Technical data

Product properties

Product type	Die
Compression	Square crimp
Min. cross section	0.14 mm ²
Max. cross section	4 mm ²

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 4 mm ²
-----------------------------	--

Material specifications

Color	black
Material	Steel
Coating	nickel-plated

Cable/line

External cable diameter	0.5 mm ... 2.4 mm
-------------------------	-------------------

CF 500/DIE TC 4 - Crimp insert

1212237

<https://www.phoenixcontact.com/us/products/1212237>



Classifications

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF 500/DIE TC 4 - Crimp insert



1212237

<https://www.phoenixcontact.com/us/products/1212237>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com