
CF 500/DIE AI 25 - Crimp insert

1212239

https://www.phoenixcontact.com/us/products/1212239

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die for CF 500 automatic crimping device, for ferrules (A... and AI...) 10.16 mm^2 and 25 mm^2

Commercial data

Item number	1212239
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356449847
Weight per piece (including packing)	71.5 g
Weight per piece (excluding packing)	71.5 g
Customs tariff number	84799070
Country of origin	DE

Technical data

Product properties

Product type	Die
Compression	WM crimp
Min. cross section	10.16 mm²
Max. cross section	25 mm²

Connection data

Conductor connection

Cross section range, metric	10 mm² ... 25 mm²

Material specifications

Color	black (RAL 9005)
Material	Steel

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212239

EAC
Approval ID: RU C-DE.AI30.B.01549

Classifications

ECLASS

ECLASS-13.0	17130192
ECLASS-15.0	17130192

ETIM

ETIM 10.0	EC002778

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	16.803 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com