CRIMPFOX-C120 RCT 70-1/DIE - Crimp insert

1212319

https://www.phoenixcontact.com/us/products/1212319

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die (pair), for CRIMPFOX-C120, for copper tube lug 10 + 70 mm^2, WM crimp

Commercial data

Item number	1212319
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Z
GTIN	4046356454650
Weight per piece (including packing)	135.8 g
Weight per piece (excluding packing)	135.8 g
Customs tariff number	82079091
Country of origin	DE

Technical data

Product properties

Product type	Die
Compression	HEX crimp
Product property	Replacement insert for CRIMPFOX-C120 crimping pliers
Min. cross section	10 mm²
Max. cross section	70 mm²
AWG min	7
AWG max	2/0

Connection data

Conductor connection

Cross section range, metric	10 mm² ... 70 mm²

Material specifications

Color	black

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212319

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-15.0	21043892
ECLASS-13.0	21043892

ETIM

ETIM 10.0	EC011822

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	5.87 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com