

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool case, lockable, with adjustable strap, equipped with: cable cutter, diagonal cutter, micro cutter, stripping tools, crimping tool set, combination, needle-nose, and water pump pliers, VDE bladed and Phillips screwdrivers, control cabinet key, voltage tester, ferrule box, blades, tape measure, continuity tester, marking tool, ring and open-end wrench set, adjustable wrench, hex key set, safety glasses, hammer, 47-piece ratchet socket wrench set, 1/4"

Commercial data

Item number	1212629
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4046356652483
Weight per piece (including packing)	13,280 g
Weight per piece (excluding packing)	13,280 g
Customs tariff number	82060000
Country of origin	DE

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



Set consists of

CUTFOX 12 - Cable-cutting tool

1212128

<https://www.phoenixcontact.com/us/products/1212128>



Cable cutter, for copper and aluminum up to 12 mm diameter (up to 35 mm²)

CUTFOX-S VDE - Diagonal cutter

1212207

<https://www.phoenixcontact.com/us/products/1212207>



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/us/products/1212489>



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>

WIREFOX-D 13 - Stripping tool

1212162

<https://www.phoenixcontact.com/us/products/1212162>



Stripping tool, for stripping installation lines of \varnothing 8 - 13 mm , e.g. NYM 3 x 1.5 mm² to 5 x 2.5 mm², single line stripping 0.2 mm² - 4 mm² , with longitudinal cut blade and sliding knife

WIREFOX-D 28 - Stripping tool

1212174

<https://www.phoenixcontact.com/us/products/1212174>



Stripping tool, for stripping lines of \varnothing 8 - 28 mm

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



WIREFOX-D 11 - Stripping tool

1212160

<https://www.phoenixcontact.com/us/products/1212160>



Stripping tool, for stripping multicore signal, control and fiberglass wires of \varnothing 2.5 - 11 mm. Insulation thickness up to 1 mm

CRIMPFOX-M SET - Crimping pliers set

1212093

<https://www.phoenixcontact.com/us/products/1212093>



Crimping pliers set, consisting of CRIMPFOX-M (pliers) and dies for insulated cable lugs 0.5 ... 2.5 mm² (1212074), non-insulated conduit lugs 0.5 ... 6 mm² (1212079) and ferrules 0.25 ... 10 mm² (1212080) and 16/25 mm² (1212081).

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



CRIMPFOX-M RCI 6/DIE - Crimp insert

1212073

<https://www.phoenixcontact.com/us/products/1212073>



Die, for Crimpfox-M, for insulated cable lugs 0.1 - 0.4 mm² and 4 - 6 mm² (light green, yellow), packed in a serial storage box

UNIFOX-C VDE - Combination pliers

1212202

<https://www.phoenixcontact.com/us/products/1212202>



Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



UNIFOX-P VDE - Needle-nose pliers

1212204

<https://www.phoenixcontact.com/us/products/1212204>



Needle-nose pliers with blade, notched grip area,
VDE 1000 V AC/1500 V DC tested

UNIFOX-WP - Water pump pliers

1212365

<https://www.phoenixcontact.com/us/products/1212365>



Water pump pliers, with groove joint, grip areas with dual notching, acc. to
VDE ISO 8976

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>

SZS 0,4X2,5 VDE - Screwdriver

1205037

<https://www.phoenixcontact.com/us/products/1205037>



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

SZS 0,5X3,0 VDE - Screwdriver

1207404

<https://www.phoenixcontact.com/us/products/1207404>



Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



SZS 1,0X4,0 VDE - Screwdriver

1205066

<https://www.phoenixcontact.com/us/products/1205066>



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

SZS 1,0X6,5 VDE - Screwdriver

1205079

<https://www.phoenixcontact.com/us/products/1205079>



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>

SZK PH0 VDE - Screwdriver

1205147

<https://www.phoenixcontact.com/us/products/1205147>



Screwdriver, PH crosshead, VDE insulated, size: PH 0 x 80 mm, 2-component grip, with non-slip grip

SZK PH1 VDE - Screwdriver

1205150

<https://www.phoenixcontact.com/us/products/1205150>



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>

SZK PH2 VDE - Screwdriver

1205163

<https://www.phoenixcontact.com/us/products/1205163>



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

DUSPOL EXPERT - Voltage tester

1209091

<https://www.phoenixcontact.com/us/products/1209091>



Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



USS 4 - Control cabinet key

1203149

<https://www.phoenixcontact.com/us/products/1203149>



Control cabinet key, metal, for all common types of control cabinet

AI SORTI BOX RD - Assortment box

3202960

<https://www.phoenixcontact.com/us/products/3202960>



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



AI-TWIN SORTI BOX BU - Assortment box

3202986

<https://www.phoenixcontact.com/us/products/3202986>



Assortment box, supplied with TWIN ferrules in accordance with DIN 46228-4, 50 pcs. each AI-TWIN 2x0,5-8 WH, AI-TWIN 2x0,75-8 GY, AI-TWIN 2x1-8 RD, AI-TWIN 2x1,5-8 BK, 25 pcs. AI-TWIN 2x2,5-10 BU

TOOL-CASE EMPTY - Toolbox

1212628

<https://www.phoenixcontact.com/us/products/1212628>



Tool case, unequipped, can be locked, with rubber straps to hold tools in place

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



SF-LHEX SET - Tool set

1212544

<https://www.phoenixcontact.com/us/products/1212544>



Offset screwdriver set, hex, metric, SW 1.5; 2; 2.5; 3; 4; 5; 6; 8, and 10 mm, with ball head, matt chrome-plated, 9-part, in practical holder

SF-SOCKET SET 47 - Tool set

1200292

<https://www.phoenixcontact.com/us/products/1200292>



1/4" socket set, 47-piece, 1/4" reversible ratchet, 48 teeth with fast locking system, 50 mm and 100 mm 1/4" extensions, 1/4" screwdriver handle, 150 mm 1/4" flexible extension, 1/4" Cardan joint, 1/4" T-handle
2 x 1/4" bit adapter, 13 knurled 1/4" sockets, wrench size: 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, 21 knurled socket bits: 6 x Torx® T10, T15, T20, T25, T30, T40, 6 x Hex 3, 4, 5, 6, 7, 8 mm, 3 x Phillips recess® PH1, PH2, PH3, 3 x Pozidriv® PZ1, PZ2, PZ3, 3 x slotted 4, 5.5, 7 mm, Allen wrench Hex 1.27, 1.5, 2, 2.5 mm, breakage and impact-resistant plastic case with metal fastening

TOOL-CASE - Toolbox



1212629

<https://www.phoenixcontact.com/us/products/1212629>

Technical data

Notes

General	Tool case
Environmental Product Compliance	
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Type of packaging	Case

Dimensions

Width	260 mm
Height	270 mm
Depth	260 mm
Length	510 mm

Material specifications

Color	black (RAL 9005)
Material	Polyester

TOOL-CASE - Toolbox

1212629

<https://www.phoenixcontact.com/us/products/1212629>



Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 10.0	EC000149
-----------	----------

UNSPSC

UNSPSC 21.0	27113200
-------------	----------

TOOL-CASE - Toolbox



1212629

<https://www.phoenixcontact.com/us/products/1212629>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com