

# CRIMPFOX-DSUB 5-1 - Crimping pliers



1212711

<https://www.phoenixcontact.com/us/products/1212711>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for rolled D-SUB contacts, standard, 0.05 mm<sup>2</sup> - 0.5 mm<sup>2</sup>, incl. contact locator

The figure shows a version of the article

## Your advantages

- Unlockable pressure lock
- Lateral conductor entry
- Crimping pliers for processing D-SUB contacts

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212711       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3136        |
| GTIN                                 | 4046356857604 |
| Weight per piece (including packing) | 447 g         |
| Weight per piece (excluding packing) | 444.44 g      |
| Customs tariff number                | 82032000      |
| Country of origin                    | SE            |

# CRIMPFOX-DSUB 5-1 - Crimping pliers



1212711

<https://www.phoenixcontact.com/us/products/1212711>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                  |                               |
|------------------|-------------------------------|
| Product type     | Crimping tool                 |
| Compression      | B crimp                       |
| Product property | Unlockable pressure lock      |
|                  | Lateral conductor entry       |
|                  | For processing D-SUB contacts |

### Connection data

#### Conductor connection

|                             |  |
|-----------------------------|--|
| Cross section range, metric | 0.08 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> |
| Cross section range AWG     | 28 ... 22                                    |

### Dimensions

|        |        |
|--------|--------|
| Width  | 18 mm  |
| Height | 59 mm  |
| Length | 198 mm |

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

# CRIMPFOX-DSUB 5-1 - Crimping pliers



1212711

<https://www.phoenixcontact.com/us/products/1212711>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212711>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-DSUB 5-1 - Crimping pliers



1212711

<https://www.phoenixcontact.com/us/products/1212711>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX-DSUB 5-1 - Crimping pliers



1212711

<https://www.phoenixcontact.com/us/products/1212711>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)