

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, compact pliers, coaxial connectors, 0.7 mm, 1.07 mm, 1.69 mm, 3.25 mm, 4.52 mm, 5.41 mm, six marked die stations, unlockable pressure lock, lateral entry, hex crimp

The figure shows a version of the article

Your advantages

- Lateral conductor entry
- Unlockable pressure lock
- Crimping pliers for processing coaxial connectors

Commercial data

Item number	1212712
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3138
GTIN	4046356857611
Weight per piece (including packing)	618.3 g
Weight per piece (excluding packing)	618.3 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	HEX crimp
Product property	Lateral conductor entry
	Unlockable pressure lock
	Crimping pliers for processing coaxial connectors

Crimping position 1

Crimping width 3.25 mm

Crimping position 2

Crimping width 4.52 mm

Crimping position 3

Crimping width 5.41 mm

Crimping position 4

Crimping width 1.69 mm

Crimping position 5

Crimping width 1.07 mm

Crimping position 6

Max. cross section 0.7 mm²

Connection data

Conductor connection

Cross section range, metric 0.72 mm² ... 5.41 mm²

Dimensions

Width	22 mm
Height	76 mm
Length	204 mm

External dimensions

Outside diameter 0.72 mm ... 5.41 mm

Material specifications

Color	black
-------	-------

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212712>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com