# CRIMPFOX-CATV 8,23-1 - Crimping pliers

1212717

https://www.phoenixcontact.com/us/products/1212717

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for CATV connectors, 6.65 mm, 8.23 mm, 9.70 mm, three marked die stations, unlockable pressure lock, lateral entry

## Your advantages

- Unlockable pressure lock
- Lateral conductor entry
- Crimping pliers for processing coaxial CATV connectors

## Commercial data

| | |
|---|---|
| Item number | 1212717 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3138 |
| GTIN | 4046356857666 |
| Weight per piece (including packing) | 675.6 g |
| Weight per piece (excluding packing) | 675.6 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

## Technical data

### Notes

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

| | |
|---|---|
| Product type | Crimping tool |
| Compression | HEX crimp |
| Product property | Unlockable pressure lock |
| | Lateral conductor entry |
| | Crimping pliers for processing coaxial connectors |

Crimping position 1

| | |
|---|---|
| Crimping width | 6.65 mm |

Crimping position 2

| | |
|---|---|
| Crimping width | 8.23 mm |

Crimping position 3

| | |
|---|---|
| Crimping width | 9.70 mm |

### Connection data

Conductor connection

| | |
|---|---|
| Cross section range, metric | 6.65 mm² ... 9.7 mm² |

### Dimensions

| | |
|---|---|
| Width | 22 mm |
| Height | 80 mm |
| Length | 256 mm |

External dimensions

| | |
|---|---|
| Outside diameter | 6.65 mm ... 9.7 mm |

### Material specifications

| | |
|---|---|
| Color | black |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212717

**EAC**
Approval ID: RU x-DE.xx08.B.02974

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000168 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27111500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com