

# CRIMPFOX-CX 7,06 HD-M - Crimping pliers



1212718

<https://www.phoenixcontact.com/us/products/1212718>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**Crimping pliers**, compact pliers, coaxial connectors, HDTV, BNC, TNC, 1.04 mm, 4.52 mm, 6.48 mm, 7.06 mm, four marked die stations, unlockable pressure lock, lateral entry

## Your advantages

- Lateral conductor entry
- Unlockable pressure lock
- Crimping pliers for processing coaxial connectors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212718       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3138        |
| GTIN                                 | 4046356857772 |
| Weight per piece (including packing) | 620 g         |
| Weight per piece (excluding packing) | 620 g         |
| Customs tariff number                | 82032000      |
| Country of origin                    | SE            |

# CRIMPFOX-CX 7,06 HD-M - Crimping pliers



1212718

<https://www.phoenixcontact.com/us/products/1212718>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                  |   |
|------------------|---|
| Product type     | Crimping tool                                     |
| Compression      | HEX crimp   |
| Product property | Lateral conductor entry                           |
|                  | Unlockable pressure lock                          |
|                  | Crimping pliers for processing coaxial connectors |

#### Crimping position 1

Crimping width 4.52 mm

#### Crimping position 2

Crimping width 6.48 mm

#### Crimping position 3

Crimping width 7.06 mm

#### Crimping position 4

Crimping width 1.68 mm

#### Crimping position 5

Crimping width 1.04 mm

### Connection data

#### Conductor connection

Cross section range, metric 0.72 mm<sup>2</sup> ... 5.41 mm<sup>2</sup>

### Dimensions

|        |        |
|--------|--------|
| Width  | 22 mm  |
| Height | 76 mm  |
| Length | 204 mm |

#### External dimensions

Outside diameter 0.72 mm ... 5.41 mm

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

# CRIMPFOX-CX 7,06 HD-M - Crimping pliers



1212718

<https://www.phoenixcontact.com/us/products/1212718>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212718>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-CX 7,06 HD-M - Crimping pliers



1212718

<https://www.phoenixcontact.com/us/products/1212718>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX-CX 7,06 HD-M - Crimping pliers



1212718

<https://www.phoenixcontact.com/us/products/1212718>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)