

WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows WIREFOX 4 CUS

Stripping tool, laser marked according to customer specifications, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

Product description

Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212152 WIREFOX 10/SB

Your advantages

- Flexible, adjustable limit stop for the stripping length
- Practical integrated wire cutter
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1212760 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BH312V |
| GTIN | 4046356942768 |
| Weight per piece (including packing) | 214 g |
| Weight per piece (excluding packing) | 207.9 g |
| Country of origin | SE |

WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Stripping tool

Application

Abisolieren von Leitungen und Leiter

Connection data

Conductor connection

Cross section range, metric

0.02 mm² ... 10 mm² (Stripping range)

1.5 mm² (Cutting zone)

Cross section range AWG

34 ... 8 (Stripping range)

16 (Cutting zone)

Stripping length

2 mm ... 18 mm

Dimensions

Width

20 mm

Height

90 mm

Length

191 mm

Material specifications

Color

black/green

WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212760>



EAC

Approval ID: RU x-DE.xx08.B.02974

WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043706 |
| ECLASS-15.0 | 21043706 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002109 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com