

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/us/products/1212765>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser marked according to customer specifications, for ferrules according to DIN 46228 Parts 1+4, 10 mm² ... 25 mm², lateral entry, WM crimp

The figure shows CRIMPFOX-RCI
6 CUS

Your advantages

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25 %

Commercial data

Item number	1212765
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4046356942928
Weight per piece (including packing)	681.4 g
Weight per piece (excluding packing)	680.1 g
Country of origin	SE

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/us/products/1212765>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Crimping tool

Compression

WM crimp

Connection data

Conductor connection

Cross section range, metric

10 mm² ... 25 mm²

Cross section range AWG

8 ... 4

Dimensions

Width

25 mm

Height

68 mm

Length

256 mm

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/us/products/1212765>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212765>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/us/products/1212765>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX 25R CUS - Crimping pliers



1212765

<https://www.phoenixcontact.com/us/products/1212765>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com