

CRIMPFOX-RCI 6 CUS - Crimping pliers



1212774

<https://www.phoenixcontact.com/us/products/1212774>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser marked according to customer specifications, for insulated cable lugs, 0.5 mm² ... 6.0 mm² (red, blue, yellow), oval crimp, symmetrical

Your advantages

- CRIMPFOX-RCI 6 /... represent the top end of the range for cable lug crimping pliers
- Precision-manufactured dies ensure consistently high levels of quality during contact processing

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1212774 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BH313V |
| GTIN | 4046356943017 |
| Weight per piece (including packing) | 670.8 g |
| Weight per piece (excluding packing) | 670.8 g |
| Country of origin | SE |

CRIMPFOX-RCI 6 CUS - Crimping pliers



1212774

<https://www.phoenixcontact.com/us/products/1212774>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

| | |
|--------------|---------------|
| Product type | Crimping tool |
| Compression | Oval crimp |

Crimping position 1

| | |
|--------------------|---------------------|
| Min. cross section | 0.5 mm ² |
| Max. cross section | 1.5 mm ² |
| AWG min | 20 |
| AWG max | 16 |

Crimping position 2

| | |
|--------------------|---------------------|
| Min. cross section | 1.5 mm ² |
| Max. cross section | 2.5 mm ² |
| AWG min | 16 |
| AWG max | 14 |

Crimping position 3

| | |
|--------------------|-------------------|
| Min. cross section | 4 mm ² |
| Max. cross section | 6 mm ² |
| AWG min | 12 |
| AWG max | 10 |

Connection data

Conductor connection

| | |
|-----------------------------|---|
| Cross section range, metric | 0.5 mm ² ... 6 mm ² |
| Cross section range AWG | 20 ... 10 |

Dimensions

| | |
|--------|--------|
| Width | 25 mm |
| Height | 68 mm |
| Length | 256 mm |

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

CRIMPFOX-RCI 6 CUS - Crimping pliers



1212774

<https://www.phoenixcontact.com/us/products/1212774>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212774>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-RCI 6 CUS - Crimping pliers



1212774

<https://www.phoenixcontact.com/us/products/1212774>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX-RCI 6 CUS - Crimping pliers



1212774

<https://www.phoenixcontact.com/us/products/1212774>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com