

# CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser marked according to customer specifications, for insulated cable lugs, 0.5 mm<sup>2</sup> ... 6.0 mm<sup>2</sup> (red, blue, yellow), oval crimp, asymmetrical

The figure shows CRIMPFOX-RCI  
6 CUS

## Your advantages

- CRIMPFOX-RCI 6 /... represent the top end of the range for cable lug crimping pliers
- Precision-manufactured dies ensure consistently high levels of quality during contact processing

## Commercial data

Item number	1212775
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4046356943024
Weight per piece (including packing)	680.47 g
Weight per piece (excluding packing)	680.47 g
Country of origin	SE

# CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Crimping tool

Compression

Oval crimp

#### Crimping position 1

Min. cross section

0.5 mm<sup>2</sup>

Max. cross section

1.5 mm<sup>2</sup>

AWG min

20

AWG max

16

#### Crimping position 2

Min. cross section

1.5 mm<sup>2</sup>

Max. cross section

2.5 mm<sup>2</sup>

AWG min

16

AWG max

14

#### Crimping position 3

Min. cross section

4 mm<sup>2</sup>

Max. cross section

6 mm<sup>2</sup>

AWG min

12

AWG max

10

### Connection data

#### Conductor connection

Cross section range, metric

0.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>

Cross section range AWG

20 ... 10

### Dimensions

Width

25 mm

Height

68 mm

Length

256 mm

### Material specifications

Color

black

# CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212775>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)