KP ICS25X122 K4 C3 P5 - Membrane keypad

1215684

https://www.phoenixcontact.com/us/products/1215684

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Membrane keypad for ICS25x122, self-adhesive, conductive silver technology, 4 keys, 2 colors, 5-position connection lug, pitch: 1.0 mm, transparent window for 0.96″ TFT display



Your advantages

- Housing system for visualization and operation in the control cabinet
- Customization of membrane keypad via configurator
- Coordinated housings, keypads, and displays
- Positioning of the display using the configurator

Commercial data

Item number	1215684
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC09
Product key	ACHAEJ
GTIN	4063151295776
Weight per piece (including packing)	4.62 g
Weight per piece (excluding packing)	2.04 g
Customs tariff number	85371098
Country of origin	DE

Technical data

Product properties

Product type	Membrane keypad
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ICS
Product family	ICS25
Technology	Conductive silver/graphite (T6/4 Cu/Ag)
Number of positions	5
Pitch	1 mm
Number of keys	4 (2 x 2)

Dimensions

Pitch	1 mm
Dimensions	22 mm x 103 mm
	11 mm x 22 mm (LCD cutout)

Material specifications

Material	Polyester

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Specification	VDMA 24364:2018-05
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Mounting

Mounting type	adhesive

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com