

PTFIX 2X2,5 BU-EX - Monoblock



1221490

<https://www.phoenixcontact.com/us/products/1221490>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Monoblock, Ex e-certified basic terminal block, mounting type: for snapping onto a DIN rail adapter, Direct mounting with flange, Free-hanging, color: blue

Your advantages

- Ex e certified
- Flexible use, thanks to DIN rail mounting, direct mounting or adhesive mounting
- Time-saving conductor connection, thanks to tool-free Push-in direct connection technology
- Clear wiring, thanks to eleven different color variants
- Space savings of up to 50 % on the DIN rail, thanks to transverse mounting

Commercial data

Item number	1221490
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE09
Product key	BEA111
GTIN	4063151309060
Weight per piece (including packing)	3.884 g
Weight per piece (excluding packing)	3.884 g
Customs tariff number	85369010
Country of origin	PL

PTFIX 2X2,5 BU-EX - Monoblock



1221490

<https://www.phoenixcontact.com/us/products/1221490>

Technical data

Product properties

Product type	Distributor terminal block
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Stripping length	8 mm ... 10 mm
------------------	----------------

Ex data

Rated data (ATEX/IECEx)

Identification	Ex II 2 G Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	3274054 PTFIX-NS35
	3274056 PTFIX-NS35A
	3274057 PTFIX-NS35A-FIX
	3274058 PTFIX-NS15A
	3274059 PTFIX-NS15A-FIX
	3274060 PTFIX-F
	3022276 CLIPFIX 35-5
	3022218 CLIPFIX 35
	3022263 CLIPFIX 15
	1204517 SZF 1-0,6X3,5
Ex temperature increase	40 K (20 A / 2.5 mm²)
Rated insulation voltage when mounting on DIN rails	400 V
Rated insulation voltage when directly mounted on mounting surface	400 V
output	(Permanent)

Ex level General

Rated voltage when mounting on DIN rails	440 V
Rated voltage during direct mounting on mounting surface	440 V
Rated current	20 A (2.5 mm²)
Maximum load current	23 A (4 mm²)
Contact resistance	0.8 mΩ

PTFIX 2X2,5 BU-EX - Monoblock



1221490

<https://www.phoenixcontact.com/us/products/1221490>

Ex connection data General

Nominal cross section	2.5 mm ²
Rated cross section AWG	14
Connection capacity rigid	0.14 mm ² ... 4 mm ²
Connection capacity AWG	26 ... 12
Connection capacity flexible	0.14 mm ² ... 2.5 mm ²
Connection capacity AWG	26 ... 14

Dimensions

Width	5.2 mm
Height	28.6 mm
Depth	21.7 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	for snapping onto a DIN rail adapter
	Direct mounting with flange
	Free-hanging

PTFIX 2X2,5 BU-EX - Monoblock

1221490

<https://www.phoenixcontact.com/us/products/1221490>



Drawings

Circuit diagram



PTFIX 2X2,5 BU-EX - Monoblock



1221490

<https://www.phoenixcontact.com/us/products/1221490>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1221490>



IECEx

Approval ID: IECExSEV21.0023U



ATEX

Approval ID: SEV21ATEX0557U



UKCA-EX

Approval ID: CML 22UKEX3672U



CCC

Approval ID: 2026322303007145

PTFIX 2X2,5 BU-EX - Monoblock



1221490

<https://www.phoenixcontact.com/us/products/1221490>

Classifications

ECLASS

ECLASS-13.0	27250118
ECLASS-15.0	27250118

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PTFIX 2X2,5 BU-EX - Monoblock



1221490

<https://www.phoenixcontact.com/us/products/1221490>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com