

# RC-06P1N8A8049X - Cable connector



1240371

<https://www.phoenixcontact.com/us/products/1240371>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.  
product version

M23, Cable connector, application: Signal, straight, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 6.5 mm ... 7.5 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Commercial data

Item number	1240371
Packing unit	20 pc
Minimum order quantity	1 pc
Product key	ABRAFA
GTIN	4063151436001
Weight per piece (including packing)	72.07 g
Weight per piece (excluding packing)	65.843 g
Country of origin	DE

# RC-06P1N8A8049X - Cable connector



1240371

<https://www.phoenixcontact.com/us/products/1240371>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 2 mm separately
--------------------	----------------------------------------

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 2 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Flammability rating according to UL 94	V0
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Number (Contact group 1)	6
Contact diameter (Contact group 1)	2 mm
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Note	Order contact inserts separately
Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	Metal
Degree of protection (plugged in)	IP65 IP67 IP68

#### Seal

External cable diameter	6.5 mm ... 7.5 mm
-------------------------	-------------------

# RC-06P1N8A8049X - Cable connector



1240371

<https://www.phoenixcontact.com/us/products/1240371>

## Environmental and real-life conditions

### Ambient conditions

Permissible humidity (storage/transport)
------------------------------------------

50 % ... 65 %
---------------

# RC-06P1N8A8049X - Cable connector

1240371

<https://www.phoenixcontact.com/us/products/1240371>

## Drawings

Schematic diagram



Connector pin assignment

# RC-06P1N8A8049X - Cable connector



1240371

<https://www.phoenixcontact.com/us/products/1240371>

## Classifications

### ECLASS

ECLASS-13.0

27440116

### ETIM

ETIM 9.0

EC002635

# RC-06P1N8A8049X - Cable connector



1240371

<https://www.phoenixcontact.com/us/products/1240371>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)