

RC-1RS1N121L00X - Cable connector



1241599

<https://www.phoenixcontact.com/us/products/1241599>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos. product version, with standard DIN cable gland

M23, Cable connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1241599
Packing unit	20 pc
Minimum order quantity	1 pc
Product key	ABRAFA
GTIN	4063151442422
Weight per piece (including packing)	101.7 g
Weight per piece (excluding packing)	95.206 g
Country of origin	DE

RC-1RS1N121L00X - Cable connector



1241599

<https://www.phoenixcontact.com/us/products/1241599>

Technical data

Product properties

Product type	Circular connector (cable-side)
Type of the screw connection	IP68 screw
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
--	----

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Mechanical properties

Mechanical data

Type of the screw connection	IP68 screw
------------------------------	------------

Connector

Insulating body

Coding	N
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	19
Direction of rotation	Standard
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67

RC-1RS1N121L00X - Cable connector



1241599

<https://www.phoenixcontact.com/us/products/1241599>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

RC-1RS1N121L00X - Cable connector



1241599

<https://www.phoenixcontact.com/us/products/1241599>

Classifications

ECLASS

ECLASS-13.0

27440116

ETIM

ETIM 9.0

EC003569

RC-1RS1N121L00X - Cable connector



1241599

<https://www.phoenixcontact.com/us/products/1241599>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com